

OVENCURE CERAMIC COATINGS - RAL8000 4 OZ. OVEN CURE KIT

Tough, Durable Coatings For Maximum Protection

State-of-the-art, Cerakote™ Firearm Coatings provide a durable, weather- and corrosion-proof, ceramic-based protective finish that resists scratching, chipping, and abrasive cleaning solvents. Hardener and paint chemically bond into an ultra-thin coating that adheres to almost any surface for a clean, professional finish. Apply with an airbrush or HVLP touch-up gun for a smooth finish. Oven Cure Kit requires oven baking for 2 hours at 250° for optimal cure or 1 hour at 300° for quick cure. For heat-sensitive materials such as plastics, a 2 hour cure at 200° is adequate.



Items cannot be shipped to New Zealand or Australia.

Attributes

- Name: RAL8000 4 OZ. OVEN CURE KIT
- Manufacturer: CERAKOTE
- Product no.: 100044083
- Mfr. No.: H-8000PK
- Color: RAL8000
- Delivery weight: 0.608kg
- Shipping height: 140mm
- Shipping width: 191mm
- Shipping length: 235mm

Item details

Made in USA

Table of Contents

- [Startpage](#)
- [English: CERAKOTE OVENCURE CERAMIC COATINGS RAL8000 4 OZ. OVEN CURE KIT Safety Instructions](#)

CERAKOTE OVENCURE CERAMIC COATINGS

RAL8000 4 OZ. OVEN CURE KIT Safety Instructions

Introduction

Thank you for choosing the CERAKOTE OVENCURE CERAMIC COATINGS RAL8000 4 OZ. OVEN CURE KIT. This guide provides essential safety instructions to ensure the safe and effective use of this product. Please read all instructions carefully before use.

General Safety Guidelines

- Ensure that the product is used in a wellventilated area to avoid inhalation of fumes.
- Keep the product out of reach of children and pets.
- Always wear appropriate personal protective equipment (PPE), including gloves and safety goggles, when handling the product.
- Do not eat, drink, or smoke while using this product.
- Follow all local regulations regarding the use and disposal of chemical products.
- Store the product in a cool, dry place away from direct sunlight and heat sources.

Specific Safety Precautions for Use

- Avoid contact with skin and eyes. In case of contact, rinse immediately with plenty of water and seek medical advice.
- Use only in accordance with the instructions provided in this manual.
- Ensure that the oven used for curing is clean and free from any flammable materials.
- Do not exceed the recommended curing temperatures and times as stated in the product specifications.
- Be cautious of fumes produced during the curing process. Ensure proper ventilation or use a respirator if necessary.

Instructions for Installation and Usage

1. Preparation:

- Ensure the surface to be coated is clean, dry, and free from grease or contaminants.
- Shake the Cerakote thoroughly before use.

2. Mixing:

- Mix the Cerakote with the hardener in the provided graduated cylinder according to the instructions on the product label.
- Use the funnel filter to pour the mixture into the airbrush or HVLP touchup gun.

3. Application:

- Apply the mixed Cerakote using an airbrush or HVLP touchup gun for an even and smooth finish.
- Avoid applying too thick a layer to prevent runs and drips.

4. Curing:

- Place the coated item in a preheated oven.
- Cure at 250°F (121°C) for 2 hours for optimal results or at 300°F (149°C) for a quick cure of 1 hour.
- For heatsensitive materials, cure at 200°F (93°C) for 2 hours.

5. Cooling:

- Allow the coated item to cool completely before handling.

Disposal Instructions

- Dispose of any unused product and containers in accordance with local regulations.
- Do not pour leftover product down the drain or throw it in the regular trash.
- Check with local waste management authorities for proper disposal methods for hazardous materials.

Contact Information for Further Support

For safety inquiries or further assistance, please contact the manufacturer's customer service or visit their official website. Ensure that you have the product name and details available when making inquiries.

Thank you for your attention to these safety instructions. Your safety and satisfaction are our top priorities. Enjoy using your CERAKOTE OVENCURE CERAMIC COATINGS RAL8000 4 OZ. OVEN CURE KIT!